



adorne Collection
adorne® Paddle Switch with Gloss White Wall Plate, White
Part No. ASPD1532W4WP



A modern upgrade that takes as little as 10 minutes, this designer switch from the adorne Collection features smooth paddle action to turn lights on/off with ease. Use alone for control of a light or fixture from a single switch, or combine with another switch or dimmer for control from multiple locations. Coordinating screwless Wall Plate included, for a sleek and contemporary aesthetic.

Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Replaces a traditional switch in as little as 10 minutes

More color options available to fit any style, including finishes to match current hardware and lighting trends

A modern and stylish upgrade for any space, featuring smooth paddle action for turning lights on and off with ease

Offers installation flexibility, working in both single-pole and 3-way applications

Screwless Wall Plate included; Coordinate with other designer switches and outlets available from the adorne® Collection for a cohesive, contemporary look

Specifications

General Info

| | | | |
|--------------------|----------------|---------------|---------------------------|
| Product Line | Pass & Seymour | Color | White |
| Country Of Origin | China | Switch Type | Paddle |
| Number of Switches | 1 | Warranty Type | Limited Lifetime Warranty |

Dimensions

| | | | |
|-------------------|---------|------------------|--------|
| Product Width US | 3.45 in | Product Depth US | 1.5 in |
| Product Height US | 5.13 in | | |

Technical Information

| | | | |
|-----------------|---|----------|------|
| Number of Gangs | 1 | Amperage | 15 A |
|-----------------|---|----------|------|

| | | | |
|-----------------|--------------------|-----------------|--------------------------|
| Number of Poles | 3-Way, Single Pole | Mounting Type | Box |
| Voltage | 120.0 V | Connection Type | Internal Pressure Plates |
