



**Wattstopper**  
**DLM Wired Standard Shade Switch, 1B 1R, Light Almond**  
Part No. BCS\_WA\_LMSH-SW211-LA



LMSH-SW2xx Series Wall Switches are low voltage devices for manual control of shades from one or more locations. They are part of a Digital Lighting Management (DLM) system and can control any shade motors connected to DLM shade controllers

## Features & Benefits

Switches are pre-engraved with most common control configurations

Low voltage pushbutton switches for control of multiple shades

Plug n' Go automatic configuration along with Pull n' Save and Push n' Learn for system personalization

Plug to other components using Cat 5e cables with RJ45 connectors eliminating wiring errors

Matches 200-Series DLM lighting control switches for consistent design of lighting and shade control

Includes system configuration button for easy system programming from the switch

IR transceiver for wireless configuration and remote control

Components of Digital Lighting Management integrated shade control system

Custom engraving or engraved and non-engraved button kits available

## Specifications

### General Info

Product Line	Wattstopper	Color	Light Almond
Finish	Matte	UPC Number	754182000487
Country Of Origin	United States	Product Series	LMSW-SH
Switch Type	Push, Rocker	Number of Switches	1
Application Sector	Commercial	Standard	UL, cUL, FCC part 15, RoHS
Warranty Type	5-Year	Type	Switch

Dimensions

Product Width US	1.6 in	Product Weight US	0.1 lb
Product Volume US	20.3 cu in	Product Depth US	1.6 in
Product Height US	4.1 in		

Additional Information

Product Has Potential to Contribute to LEED	Yes
---	-----

Technical Information

Operating Temperature Min	0 °C	Compatibility	DLM Wired
Seismic Tested	No	Has Battery	No
Operating Temperature Max	55 °C	Number of Buttons	1
Number of Rockers	1	Topology	Free Topology
Input Voltage	24 VDC	Indoor/Outdoor	Indoor
Wattage	0.12 W	Mounting Type	J-Box
Current Draw	5 mA	Operating Temperature	0°-55°C, 32°-131°F
Operating Humidity	5-95% RH (Non-Condensing)	Wire Connection Type	RJ-45
Engraving Type	Icon	Environmental Conditions	5 to 95% (relative humidity, non-condensing)
Storage Temperature	23° - 176° F, -5° - 80° C		