



Wiremold
AV FL POKE-THRU ASY/20A/BK/LJB/TC
Part No. AV3ATCBK-LJB



Flush Style AV3 Poke-Thru Devices are an excellent solution for bringing communication and A/V services to the workstation in an open space, above-grade floor environment. All Wiremold Flush Style Poke-Thru Devices come with built-in TopGuard™ protection, an industry-leading design that meets and exceeds UL scrub water exclusion requirements for tile and carpet floors. Topguard protection prevents water, dirt, or debris from entering not just the power devices, but also the communication devices. All Wiremold Flush Style Poke-Thru Devices can be installed on tile, carpet, or wood covered floors. Each of these devices provides an excellent solution for both new or retrofit construction, with typical applications that include office buildings, airports, malls, shopping centers, libraries, and schools.

Features & Benefits

A/V device includes one prewired 20A duplex receptacle which can be wired as a standard receptacle or isolated ground	Includes one Extron bezel to accept Extron MAAP mini architectural adapter plates
(Extron devices sold separately, only through authorized Extron dealers)	Includes Ortronics® TracJack and Series II mounting adapters and Wiremold Open System adapters and inserts

Specifications

General Info

Product Line	Wiremold	UPC Number	786564016045
Country Of Origin	Mexico	Construction	Assembled
Application Sector	Commercial, Education, Healthcare, Hospitality	Standard	UL Fire Classified, cULus, NEC
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Poke-Thru

Dimensions

Product Weight US	6.619 lb	Core Hole Size	4 in
Knockout Size	1-1/4 in, 3/4 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

Trade Programs

USMCA Yes

Additional Information

RoHS Compliant Yes

Technical Information

Floor Type	Carpet, Tile, Wood	Service Capacity	Dual
Fire Rating	2 hr	Cable Entry	3/4 conduit stem for power and 1-1/4 conduit stem for low voltage
Number of Outlets	2		