



The Wiremold 2000 Series raceway offers a selection of steel, aluminum, and nonmetallic raceways that provide a versatile solution for many applications. Plugmold sections offer single or alternating circuits, in standard or isolated ground receptacles. The ScuffCoat finish is scratch resistant and protects against nicks and chips while preventing color from fading.

Features & Benefits

- USB charging- Dual-port charging modules share 2.4 amps of charging capacity and can charge multiple phones, tablets or other mobile devices at the same time.
- Multiple colors and finishes- Painted finishes of black, gray, ivory, and white, as well as anodized aluminum and stainless steel versions integrate easily with any room decor.
- Compact design- Low-profile design installs in tight locations while offering multiple power and USB charging connections. Receptacle spacing accommodates bulky AC adapters.
- Tamper-resistant receptacles- Prevents the insertion of foreign objects into receptacles reducing the risk of shocks or electrocution. Meets 2014 NEC section 406 requirements.

Specifications

General Info

| | | | |
|-----------------------|---|--------------------|---|
| Product Line | Wiremold | Color | Black |
| UPC Number | 786776184433 | Country Of Origin | United States |
| Material | Steel | Product Series | 2000 Series |
| Number of Receptacles | 3 | Features | USB-A Charging |
| Outlet Type | Tamper-Resistant | Application Sector | Commercial, Education, Entertainment, Healthcare, Hospitality, Retail |
| Standard | cULus Listed Multioutlet Assembly: File E15191 Guide PVGT/PVGT7 | Warranty Type | 1-Year from Installation or 2-Years from Day of Sale |
| Type | Plugmold | Installed Devices | Single Receptacle, USB-A Ports |

Dimensions

| | | | |
|-------------------|------------|--------------------|---------|
| Product Width US | 60.0 in | Product Weight US | 2.04 lb |
| Product Volume US | 62.1 cu in | Product Depth US | 0.75 in |
| Product Height US | 1.38 in | Receptacle Spacing | 9 in |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | E15191 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Trade Programs

| | |
|-------|-----|
| USMCA | Yes |
|-------|-----|

Additional Information

| | | | |
|----------------|-----|-------------------------------|-----|
| RoHS Compliant | Yes | Product Environmental Profile | Yes |
|----------------|-----|-------------------------------|-----|

Technical Information

| | | | |
|-------------------------|---------|--------------------------|------------------------|
| Is Pre-Wired | Yes | USB Wattage | 15 W |
| USB Amperage | 2.4 A | Wiring Configuration | Single Circuit |
| Number of USBs | 3 | Amperage | 15 A |
| Indoor/Outdoor | Indoor | Wiring Method | Hard-Wired |
| NEMA Configuration Code | 5-15R | Mounting Type | On Surface |
| Voltage | 125.0 V | Environmental Conditions | Dry interior locations |
