




Ortronics
10 Meters (10 m), 4 Duplex LC/PC To acclAIM/PC, 50/125 OM4 Multimode, ONFP Plenum, 8 Fiber, Distribution Harness Cable, Aqua
Part No. C80AM137S5EEM0010M



The 4 Duplex LC to acclAIM, 8 Fiber, Distribution Harness Cable, is designed to interface acclAIM adapter panels and breakout to individual Duplex LC connectors to interface active equipment or other patch panels within Network Racks, or in top of rack configurations. The acclAIM breakout cable is also a great solution for Telco Rooms, Meet Me Rooms, IDFs, Carrier rooms, Demarcations, and more as a cost-effective less time-consuming alternative to field termination.

Features & Benefits

| | |
|--|--|
| Part of an acclAIM Connectivity Solution: Typical total channel loss of 0.4 dB | Bend-insensitive fiber for optimal cable management and ease of installation |
| TIA Channel Compliant | Dust caps pre-installed |

Specifications

General Info

| | | | |
|-------------------|---------------|--------------------|-------------|
| Product Line | Ortronics | Color | Aqua |
| Country Of Origin | United States | Application Sector | Commercial |
| Warranty Type | 5-Year | Type | Fiber Cable |
| Boot Color | Black | | |

Dimensions

| | | | |
|-------------------|---------|-------------------|--------|
| Product Weight US | 0.39 lb | Product Length US | 10.0 m |
|-------------------|---------|-------------------|--------|

Technical Information

| | | | |
|------------------------|--|--------------------|-------------------|
| Fiber Optic Cable Type | OM4 | Jacket Application | Plenum Rated |
| Bend Radius | 90 mm | Jacket Rating | Plenum OFNP-Rated |
| Connector Type | Infinium acclAIM | Number of Fibers | 8 |
| Durability | Max IL of 0.3 dB at 200 cycles per TIA-568.3-E | Fiber Size | 50/125 |