




Ortronics
3 Meter (3m), acclAIM To Laser Cleaved Blunt End, 9/125 OS2 Single-Mode 8 Fiber, OFNP, Splice-On Pigtail, Yellow
Part No. C00AMC37S5J0M0003M



acclAIM Laser Cleaved, 8 Fiber, Splice-On Pigtail is used to splice with existing fiber trunks or new multifiber cable, enabling quick and easy cable runs and connection to the patch panels. The connectorized acclAIM end has been pre terminated in the factory for maximum reliability and quality results. The Laser cleaving simplifies fiber splicing which greatly decreases labor and cost.

Features & Benefits

acclAIM Splice-On Pigtails work with acclAIM pre-terminated fiber solutions, enabling Direct Mating Breakout Fusion Splice: The laser cleaved, loose tube single and acclAIM connectivity. They remove pin and polarity concerns and offer the lowest optical loss in pre-terminated fiber setups. fiber construction ensure quick, simplified, and consistent splicing

Specifications

General Info

Product Line	Ortronics	Color	Yellow
Country Of Origin	United States	Construction	Micro Array
Application Sector	Commercial	Warranty Type	5-Year
Type	Fiber Cable	Boot Color	Black

Dimensions

Product Weight US	0.12 lb	Product Length US	3.0 m
-------------------	---------	-------------------	-------

Technical Information

Fiber Optic Cable Type	OS2	Jacket Application	Plenum Rated
Bend Radius	90 mm	Jacket Rating	Plenum OFNP-Rated
Cable Diameter	3 mm	Return Loss	55 dB
Connector Type	Infinium acclAIM	Number of Fibers	8
Durability	Max IL of 0.3 dB at 200 cycles per TIA-568.3-E	Fiber Size	9/125