




Ortronics
2 Meters (2 m), 4 Duplex LC/UPC To acclAIM/UPC, 9/125 OS2 Single-Mode, ONFP Plenum, 8 Fiber, Distribution Harness Cable, Yellow
Part No. C80AM137S5JEM0002M



The 4 Duplex LC to acclAIM, 8 Fiber, Distribution Harness Cable, is designed to interface acclAIM adapter panels and breakout to individual Duplex LC connectors to interface active equipment or other patch panels within Network Racks, or in top of rack configurations. The acclAIM breakout cable is also a great solution for Telco Rooms, Meet Me Rooms, IDFs, Carrier rooms, Demarcations, and more as a cost-effective less time-consuming alternative to field termination.

Features & Benefits

Part of an acclAIM Connectivity Solution: Typical total channel loss of 0.4 dB	Bend-insensitive fiber for optimal cable management and ease of installation
TIA Channel Compliant	Dust caps pre-installed

Specifications

General Info

Product Line	Ortronics	Color	Yellow
Country Of Origin	United States	Application Sector	Commercial
Warranty Type	5-Year	Type	Fiber Cable
Boot Color	Black		

Dimensions

Product Weight US	0.08 lb	Product Length US	2.0 m
-------------------	---------	-------------------	-------

Technical Information

Fiber Optic Cable Type	OS2	Jacket Application	Plenum Rated
Bend Radius	90 mm	Jacket Rating	Plenum OFNP-Rated
Connector Type	Infinium acclAIM	Number of Fibers	8
Durability	Max IL of 0.3 dB at 200 cycles per TIA-568.3-E	Fiber Size	9/125