



acclAIM has redefined fiber architecture, replacing cassette-based solutions with direct connections, which eliminates extra components, and cost. acclAIM delivers the lowest insertion loss available on the market, the most optical headroom, improved density, flexibility and system lifecycle. The acclAIM™ Alignment Independent Multifiber (AIM) fiber interconnect system is designed to mate multiples of 8-fiber trunk cable connectors directly to arrays of twin-fiber patch cord connectors by means of a “conversion adapter”

## Features & Benefits

**Minimize Loss – Maximize Optical Headroom:** Lowest loss pre-term Solution, Minimize or eliminate need for splicing, Maximize optical headroom to overcome barriers to performance

**Smarter Design– Longer Lifecycle:** A simple design, adjustable polarity and fewer components. acclAIM delivers high performance and a multi-generational lifecycle. This means a sustainable building asset that lasts decades with just one installation.

**Ultra-High Density Plus (UHD+):** Make the most of each rack unit (RU) with UHD+ offering up to 192 fibers per RU (33% more than High Density)

**Simplify Connectivity:** No gender or pin issues—just direct connections. Direct-Mating Breakout allows acclAIM connectors to mate with 2-fiber MDC duplex patch cords. Polarity adapts to any link setup, whether preplanned, on-site, or adjusted on the fly.

**Reduce Labor – Lower Cost:** 40% faster install; 60% faster removal; Single link testing after mating; Faster moves adds & changes

**Approaching Infinite Scalability:** Based on the simplified design, unparalleled performance, and architecture flexibility, Infinium acclAIM has an almost limitless migration path

Go Live Faster

Typical Total Channel Connection Loss: MM .45 dB, SM .40 dB

## Specifications

### General Info

Product Line	Ortronics	Color	Yellow
Country Of Origin	United States	Construction	Micro Array
Application Sector	Commercial	Warranty Type	5-Year
Type	Fiber Cable	Boot Color	Black

### Dimensions

Product Length US	9.0 m	Cable Length	9 m
-------------------	-------	--------------	-----

### Technical Information

Fiber Optic Cable Type	Single-Mode	Compatibility	Infinium acclAIM
Jacket Application	Plenum Rated	Bend Radius	90 mm
Number of Ports	48	Number of Fanout Cables	6
Cable Type	Fiber Optic	Jacket Rating	FT6 Rated, OFNP Rated
Cable Diameter	2 mm	Return Loss	55 dB
Connector Type	Infinium acclAIM	Number of Fibers	48
Durability	Max IL of 0.3 dB at 200 cycles per TIA-568.3-E	Fiber Size	C