



Wattstopper
PIR Multi-Way Dimming Vacancy Sensor, 25-500W, White
Part No. CD-250-W



The CD-250 PIR Dimming Multi-way Vacancy Sensor provides preset dimming control and automatic lighting shutoff for a variety of applications including those with multiple switch locations. It is engineered to comply with specific provisions of California's Title 24-2013 energy code.

Features & Benefits

Collection consolidated to white option	Manual-on/automatic-off control with fullrange dimming and multi-way capability
Lighted pushbutton for visibility in darkened rooms	Ideal dimming and occupancy control for any small room with incandescent lighting
Adjustable time delay	

Specifications

General Info

Product Line	Wattstopper	Color	White
Finish	Glossy	UPC Number	754182924424
Country Of Origin	China	Product Series	CD-250
Features	Adjustable Time Delay, Air Gap Switch, Locator Light	Switch Type	Push
Installation Location	Wall	Included	Mounting Screws, Wire Nuts
Application Sector	Commercial	Standard	UL
Warranty Type	5-Year	Type	Sensor, Switch

Dimensions

Product Width US	1.7 in	Product Weight US	0.4 lb
Product Volume US	14.9 cu in	Product Depth US	2.0 in
Product Height US	4.2 in		

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Operating Temperature Min	32 °F	Timer Type	Trimpot
Load Rating	500 W @ 120 VAC	Has Battery	No
Sensor Coverage Pattern	180 deg	Sensor Type	Vacancy
Operating Temperature Max	104 °F	Sensor Mounting Height	4 ft
Number of Buttons	1	Number of Rockers	0
Sensor Technology	Passive Infrared (PIR)	Timer Duration	15 Seconds, 5 Minutes, 15 Minutes, 30 Minutes
Number of Poles	Multi-Location	Input Voltage	120 V
Line Frequency	60 Hz	Indoor/Outdoor	Indoor
Sensor Coverage	600 sq ft	Mounting Type	In-Wall
On Function	Manual On	Operating Temperature	0°-40°C, 32°-104°F
Operating Humidity	5-95% RH (Non-Condensing)	Sensing Range	24 x 25 ft
Wire Connection Type	Flying Leads	Engraving Type	Blank
Storage Temperature	23° - 176° F, -5° - 80° C		