



Pass and Seymour  
Discontinued - Titan Series Fluorescent 2 Wire Dimmer, Brown  
Part No. CDFB10277

Slide Dimmer, Electronic Single Pole 2Wire 10A 277V, Red



## Features & Benefits

For use with 2 wire 120V and 277V fluorescent dimming ballasts.	Field configurable wall plate system.
Labeling system.	Adjustable low end output voltage.
Shipped with protective film.	Rugged construction.
Superior ratings with a minimum of derating when ganged.	Simple to plan the rough-in.
Available in single pole slide-to-OFF and single pole/3-way preset models.	Attractive European styling.
Eye-catching packaging.	Exclusive adaptor kit to install other Decorator opening devices under the Titan: wall plate system. (See Page N-29.)
Blank center plate included.	For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brown
Country Of Origin	China	Application Sector	Commercial
Standard	cULus, California Title 24 Compliant	Type	Dimmer

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

---

Technical Information

---

Operating Cycles	100	Frequency Rating	60 Hz
Amperage	10 A	Number of Poles	Single Pole
Voltage	277.0 V	Load	Up to rating of device (including de-rating)
Environmental Conditions	Non-Condensing Humidity: Less than 95%		

---