



Commercial Spec Grade Duplex Receptacle, Side Wire 20A 125V

Features & Benefits

Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly. .032 inch thick, brass, triple-wipe power contacts for lasting retention.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Impact-resistant nylon face and thermoplastic back body.

Accepts #14 - #10 AWG solid or stranded copper or copper-clad wire. Terminal compartments isolated from each other for positive conductor containment.

Auto-ground clip assures positive ground. For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#). Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +50°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Commercial, Indoor
Application Sector	Residential/Commercial	Standard	UL 498
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
Voltage	125.0 V		
