



Pass and Seymour  
20A 125V Commercial Spec-Grade Duplex Receptacle, Side Wire, Ivory  
Part No. CR20I



Commercial Spec Grade Duplex Receptacle, Side Wire 20A 125V

## Features & Benefits

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Accepts #14 - #10 AWG solid or stranded copper or copper-clad wire.
- Auto-ground clip assures positive ground.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Impact-resistant nylon face and thermoplastic back body.
- Terminal compartments isolated from each other for positive conductor containment.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
- Operating Temperature: Maximum continuous +50°C, minimum -40°C without impact

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	UPC Number	785007119169
Country Of Origin	Mexico	Number of Receptacles	2
Application Sector	Commercial	Standard	UL 498
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor