



Pass and Seymour

Industrial Extra Heavy-Duty Spec Grade Receptacles, Corrosion-Resistant, Back & Side Wire, 20A, 125V, Yellow
Part No. CR6300



Industrial Extra Heavy-Duty Spec Grade Duplex Receptacle Corrosion-Resistant Back & Side Wire 20amp 125volt Yellow

Features & Benefits

One-piece brass mounting strap with integral ground.

Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.

Two drive screws anchor strap to back body and face.

Exclusive patented feature, circuit label on face allows permanent circuit identification.

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Impact-resistant nylon face and back body.

Oversized #10 deep tri-drive head brass terminal and ground screws.

Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.

Line terminals accept #14 -- #10 AWG stranded or solid copper clad conductors.

Auto-ground clip assures positive ground.

Corrosion-resistant models have nickel-plated straps and contacts.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Color	Yellow	UPC Number	785007630046
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Industrial	Standard	cULus UL498, CSA C22.2 No. 42

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	140596
--------------	-----	---------------------	--------

Technical Information

Number of Poles	Double Pole	Voltage	125 V
Connection	Back and side wire	Dielectric Strength	Withstands 2000V minimum

Temperature Rating	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact	Wire Size	#14 - #10
Number of Wires	3	Environmental Conditions	Flammability: UL94 V2
