



Pass and Seymour
15A 125V Commercial Spec-Grade Duplex Receptacle, Back and Side Wire, Ivory
Part No. CRB5262I



Construction Spec Grade Duplex Receptacle Back and Side Wire 15A 125V

Features & Benefits

Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.

Impact-resistant nylon face and thermoplastic back body.

Terminal compartments isolated from each other for positive conductor containment.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

8 hole internal screw-pressure-plate back wire terminals accept #10 - #14 AWG solid or stranded copper or copper-clad conductors.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

| | | | |
|--------------------|----------------|-----------------------|-----------------|
| Product Line | Pass & Seymour | Color | Ivory |
| Finish | Matte | UPC Number | 785007210156 |
| Country Of Origin | Mexico | Number of Receptacles | 2 |
| Application Sector | Commercial | Standard | UL 498, FEDSPEC |

| | | | |
|---------------|-------------------------|------|--------|
| Warranty Type | 1-Year Limited Warranty | Type | Outlet |
|---------------|-------------------------|------|--------|

Dimensions

| | | | |
|-------------------|----------|------------------|---------|
| Product Width US | 1.322 in | Product Depth US | 0.78 in |
| Product Height US | 2.635 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|-----------|-------|-----------------|-------------|
| Amperage | 15 A | Number of Poles | Double Pole |
| Wire Size | 4 AWG | Indoor/Outdoor | Indoor |