



Pass and Seymour
15A 125V Commercial Spec-Grade Duplex Receptacle, Back and Side Wire, Red
Part No. CRB5262RED



Construction Spec Grade Duplex Receptacle Back and Side Wire 15A 125V

Features & Benefits

Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.

Impact-resistant nylon face and thermoplastic back body.

Terminal compartments isolated from each other for positive conductor containment.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

8 hole internal screw-pressure-plate back wire terminals accept #10 - #14 AWG solid or stranded copper or copper-clad conductors.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

| | | | |
|-------------------|-------------------------|-----------------------|-------------------------|
| Product Line | Pass & Seymour | Color | Red |
| Country Of Origin | Mexico | Number of Receptacles | 2 |
| Outlet Type | Commercial, Indoor | Standard | UL498, CSA C22.2 No. 42 |
| Warranty Type | 1-Year Limited Warranty | Type | Outlet |

Dimensions

| | | | |
|------------------|----------|------------------|---------|
| Product Width US | 1.322 in | Product Depth US | 0.78 in |
|------------------|----------|------------------|---------|

| | |
|-------------------|----------|
| Product Height US | 2.635 in |
|-------------------|----------|

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|---------------------|--------------------------|------------|--------------------|
| Dielectric Strength | Withstands 2000V minimum | Connection | Back and side wire |
|---------------------|--------------------------|------------|--------------------|

| | | | |
|-----------------|---|--------------------|--------------|
| Number of Wires | 3 | Temperature Rating | -40° - 60° C |
|-----------------|---|--------------------|--------------|

| | | | |
|----------|------|-----------------|-------------|
| Amperage | 15 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

| | | | |
|-----------|-------------|----------------|--------|
| Wire Size | 14 - 10 AWG | Indoor/Outdoor | Indoor |
|-----------|-------------|----------------|--------|

| | | | |
|---------|---------|--------------------------|-----------------------|
| Voltage | 125.0 V | Environmental Conditions | Flammability: UL94 V2 |
|---------|---------|--------------------------|-----------------------|
