



Pass and Seymour
Hard Use Specification Grade Switch, Light Almond
Part No. CSB15AC4LA



Construction 4-Way Switch, Back and Side-Wire, 15A 120/277V.

Features & Benefits

One-piece brass alloy contact arm for reliable electrical performance.

High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.

Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.

Cam designed for fast make with positive break action to minimize arcing and prolong switch life.

Tri-drive terminal and mounting screws.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

One-piece steel strap with integral ground is plated for corrosion resistance.

Heavy-duty toggle bumpers for smooth and quiet operation.

Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.

Oversized silver alloy contacts for longer dependable switch life.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

| | | | |
|--------------------|----------------|-------------------|--------|
| Product Line | Pass & Seymour | Country Of Origin | Mexico |
| Application Sector | Commercial | Standard | UL 20 |

Dimensions

| | | | |
|-------------------|----------|------------------|----------|
| Product Width US | 1.32 in | Product Depth US | 1.073 in |
| Product Height US | 2.375 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|------------|-----|--------------|-----|
| CSA Listed | Yes | cULus Listed | Yes |
|------------|-----|--------------|-----|

Technical Information

| | | | |
|----------------|-------------------|---------------------------|--------|
| Contact Rating | 15amp, 120/277vac | Closed Contact Resistance | Toggle |
|----------------|-------------------|---------------------------|--------|

| | | | |
|----------|------|-----------------|-------|
| Amperage | 15 A | Number of Poles | 4-Way |
|----------|------|-----------------|-------|

| | | | |
|---------|-----|---------|---------|
| Wattage | 4 W | Voltage | 120.0 V |
|---------|-----|---------|---------|
