



Pass and Seymour
Commercial Specification Grade Switch, Light Almond
Part No. CS20AC3LA



Commercial 3-Way Switch, Side-Wire, 20A 120/277V. These switches offer excellent value while meeting federal specification standards. External screw-pressure-plate back wiring enables fast installation and superior electrical connections. Rugged construction shrugs off hard use and abuse.

Features & Benefits

One-piece brass alloy contact arm for reliable electrical performance.

High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.

Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.

Cam designed for fast make with positive break action to minimize arcing and prolong switch life.

Tri-drive terminal and mounting screws.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

One-piece steel strap with integral ground is plated for corrosion resistance.

Heavy-duty toggle bumpers for smooth and quiet operation.

Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.

Oversized silver alloy contacts for longer dependable switch life.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

| | | | |
|--------------------|----------------|-------------------|--|
| Product Line | Pass & Seymour | Color | Light Almond |
| Finish | Matte | Country Of Origin | Mexico |
| Application Sector | Commercial | Standard | UL Listed E140597, Standard UL20, FedSpec WS896, Flammability Rating UL94 V2 |
| Type | Switch | | |

Dimensions

| | | | |
|------------------|---------|------------------|----------|
| Product Width US | 1.32 in | Product Depth US | 1.073 in |
|------------------|---------|------------------|----------|

| | |
|-------------------|----------|
| Product Height US | 3.281 in |
|-------------------|----------|

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140597 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

| | | | |
|-----------------------|-----------------------------------|----------|--------|
| Contact Configuration | One piece brass alloy contact arm | Actuator | Toggle |
|-----------------------|-----------------------------------|----------|--------|

| | | | |
|------------|--|----------------|---------------------------------|
| Connection | Side Wire or external screw-pressure plate | Contact Rating | Oversized silver alloy contacts |
|------------|--|----------------|---------------------------------|

| | | | |
|----------|------|-----------------|-------|
| Amperage | 20 A | Number of Poles | 3-Way |
|----------|------|-----------------|-------|

| | | | |
|----------------|--------|-----------------------|------------|
| Indoor/Outdoor | Indoor | Operating Temperature | -40°-115°C |
|----------------|--------|-----------------------|------------|

| | | | |
|---------|-----------|-----------------|-------|
| Voltage | 120/277 V | Connection Type | Wired |
|---------|-----------|-----------------|-------|

| | |
|----------------------|------------------------------------|
| Degree of Protection | 1500V Dielectric Withstand Voltage |
|----------------------|------------------------------------|
