



Wattstopper  
Dual Tech Occupancy Sensor 100 -347 VAC, center mount 360 USA  
Part No. DT-355-U



Wattstopper's low profile DT-355 dual technology occupancy sensor combines the benefits of passive infrared (PIR) and ultrasonic technologies. The sensor mounts on the ceiling with a flat, unobtrusive appearance and provides 360 degrees of coverage.

## Features & Benefits

Architecturally appealing low profile appearance

Ultrasonic diffusers give more comprehensive coverage

Operates at 120, 230 (single phase), 277 or 347 VAC, 50/60 Hz

Terminal wiring for quick and easy installation

Walk-through mode increases savings potential

## Specifications

### General Info

Product Line	Wattstopper	Color	White
Finish	Glossy	UPC Number	754182925858
Country Of Origin	United States	Product Series	DT-355
Features	Adjustable Time Delay, Indicator Lights, Light Level Sensor, Sensitivity Adjustment, Test Mode, Walkthrough Mode	Switch Type	Motion Sensor
Installation Location	Ceiling	Included	Mounting Screws, Sensor Mask
Application Sector	Commercial	Standard	UL, cUL, BAA, TAA
Warranty Type	5-Year	Type	Sensor

## Dimensions

Product Width US	4.5 in	Product Weight US	0.2 lb
Product Volume US	44.4 cu in	Product Depth US	1.5 in
Product Height US	4.5 in		

Additional Information

Product Environmental Profile Yes

Technical Information

Operating Temperature Min	32 °F	Timer Type	DIP Switch
Load Rating	1200 W @ 230-347 VAC, 800 W @ 120 VAC	Compatibility	BZ Power Packs, Wattstopper PLUS Sensor Interface Module
Ultrasonic Frequency	40 kHz	Has Battery	No
Sensor Coverage Pattern	360 deg	Sensor Type	Occupancy
Operating Temperature Max	131 °F	Sensor Mounting Height	8-12 ft
Number of Buttons	0	Sensor Technology	Dual Technology, Passive Infrared (PIR), Ultrasonic
Timer Duration	30 Seconds, 5-30 Minutes	Indicator	PIR Detection LED, Ultrasonic Detection LED
Input Voltage	120/230/277/347 VAC	Line Frequency	50 Hz, 60 Hz
Indoor/Outdoor	Indoor	Sensor Coverage	1000 sq ft
Mounting Type	2-1/4 in Deep J-Box, 4 in Octagonal J-Box, Surface	On Function	Auto On

Operating Temperature	0°-55°C, 32°-131°F	Operating Humidity	5-95% RH (Non-Condensing)
Sensing Range	36 ft	Wire Connection Type	Flying Leads
Engraving Type	Blank	Storage Temperature	23° - 176° F, - 5° - 80° C