



Pass and Seymour  
Flexcor® Turnlok® EHU Strain Relief Grips, Cable Diameter 0.94 - 1.25 in.  
Part No. FC94GL



FC94GL: Extra-Hard Use, Closed Mesh, Cable Diameter 0.94 - 1.25 inches,  
Mesh Length 11.75-in

## Features & Benefits

EHU wire mesh grips provide additional strain-relief for wiring device plugs and connectors used on portable equipment in commercial and institutional applications, and industrial plant and construction site areas, which incur abnormally high abuse. Support grips are woven of corrosion-resistant tinned-stainless steel wire.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information. Mesh Length: 11.50

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Construction	Various Types of Pulling, Support and Strain Relief Grips	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)		

### Dimensions

Product Width US	1.25 in	Product Depth US	11.75 in
Product Height US	1.25 in		

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	67507
------------	-----	-----------------	-------

### Technical Information

Maximum Cable Range	0.94 in	Minimum Cable Range	1.25 in
---------------------	---------	---------------------	---------

---

Capacity

Various Cable Diameter Ranges

Mounting

Consult the Factory  
for Mounting  
Recommendations

---

Load

Strain Relief Grips are designed to prevent tension from being transferred to junctions and terminals on electrical cord, cable and conduit, therefore providing a more secure electrical structure.

---