



**Wattstopper**  
**Ultrasonic Multi-Way Resi Vacancy Sensor 600W, White, Box**  
Part No. CU-250-W



The CU-250 Ultrasonic Multi-way Vacancy Sensor provides automatic lighting shutoff for a variety of applications including those with multiple switch locations. It is engineered to comply with specific provisions of California's Title 24-2013 energy code.

## Features & Benefits

- Collection consolidated to white option
- Manual-on/automatic-off control with multi-way capability
- Lighted pushbutton for visibility in darkened rooms
- Ideal for bathrooms, L-shaped rooms and spaces with obstructions
- Adjustable sensitivity and time delay

## Specifications

### General Info

Product Line	Wattstopper	Color	White
Finish	Glossy	UPC Number	754182924370
Country Of Origin	China	Product Series	CU-250
Features	Adjustable Time Delay, Indicator Lights, Sensitivity Adjustment	Switch Type	Push
Installation Location	Wall	Included	Mounting Screws, Wire Nuts
Application Sector	Commercial, Residential	Standard	UL, cUL, Complies with 2011 NEC requirements, California Title 24 Compliant
Warranty Type	5-Year	Type	Sensor, Switch

Dimensions

Product Width US	1.7 in	Product Weight US	0.3 lb
Product Volume US	28.98 cu in	Product Depth US	1.8 in
Product Height US	4.2 in		

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Operating Temperature Min	32 °F	Timer Type	Trimpot
Load Rating	600 W @ 120 VAC	Ultrasonic Frequency	40 kHz
Has Battery	No	Sensor Coverage Pattern	180 deg
Sensor Type	Vacancy	Operating Temperature Max	122 °F
Number of Gangs	1	Sensor Mounting Height	4 ft
Number of Buttons	1	Number of Rockers	0
Sensor Technology	Ultrasonic	Timer Duration	15 Seconds, 5 Minutes, 15 Minutes, 30 Minutes
Number of Poles	3-Way, Single Pole	Indicator	Ultrasonic Detection LED
Input Voltage	120 V	Requires Neutral Wire	Yes
Line Frequency	60 Hz	Indoor/Outdoor	Indoor
Sensor Coverage	600 sq ft	Mounting Type	In-Wall
On Function	Manual On	Operating Temperature	0°-50°C, 32°-122°F
Operating Humidity	5-95% RH (Non-Condensing)	Sensing Range	Major motion 20 x 20 ft, Minor motion 15 x 15 ft

Wire Connection Type	Flying Leads	Engraving Type	Blank
Storage Temperature	23° - 176° F, -5° - 80° C		