



FS300LB: Standard Duty, Split Lace, Locking Bale (Universal Eye), Cable Diameter 3.00 - 3.49 inches, Bale Length 18-in, Mesh Length 26-in, Break Strength 5280 lbs.

Features & Benefits

Split lace support grips are used when the end of the cable cannot easily be accessed and the support grip is intended for permanent installation.

Vertical runs of no more than 100 ft.

Support grips are woven of corrosion-resistant tinned-stainless steel wire.

Bale Length: 18: Mesh Length: 26

Split lace support grips are designed for loads up to 600 lbs.

They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

Specifications

General Info

| | | | |
|--------------|---|--------------------|------------|
| Product Line | Pass & Seymour | Country Of Origin | Mexico |
| Construction | Various Types of Pulling, Support and Strain Relief Grips | Application Sector | Industrial |
| Standard | UL/CSA Approval (consult factory) | | |

Technical Information

| | | | |
|---------------------|-------------------------------|---------------------|--|
| Maximum Cable Range | 3 in | Minimum Cable Range | 3.49 in |
| Capacity | Various Cable Diameter Ranges | Mounting | Consult the Factory for Mounting Recommendations |
| Load | Approx. Break Strength: 5280 | | |