



Wattstopper
PIR Ceiling Occupancy Sensor 120 linear sq. ft. 24 VDC
Part No. CX-105-3



Wattstopper's CX-100 Series Passive Infrared (PIR) Ceiling/Wall Sensors detect occupancy to control lighting in a wide variety of applications. These sensors provide superior coverage and performance with great energy savings.

Features & Benefits

Turns lights on and off based on occupancy

User-adjustable time delay and sensitivity

ASIC technology reduces components and provides greater reliability

Choice of four coverage patterns

Built-in light level sensor

Isolated relay for use with HVAC or other control systems

Automatic or manual-on operation when used with a BZ-150 Power Pack

Specifications

General Info

Product Line	Wattstopper	Color	White
UPC Number	754182911417	Country Of Origin	China
Product Series	CX-100	Features	Adjustable Time Delay, Indicator Lights, Light Level Sensor, Power Pack Required, Sensitivity Adjustment
Installation Location	Ceiling, Wall	Included	J-Box Cover Plate, Sensor Mask, Swivel Bracket
Application Sector	Commercial	Standard	UL, cUL, ISO 9002
Warranty Type	5-Year	Type	Sensor

Dimensions

Product Width US	3.4 in	Product Weight US	0.4 lb
Product Volume US	38.1 cu in	Product Depth US	3.3 in
Product Height US	3.4 in		

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Compatibility	EN-SIM-AI/SPS-GB2-BK	Has Battery	No
Sensor Type	Occupancy	Sensor Mounting Height	30 ft
Sensor Technology	Passive Infrared (PIR)	Indicator	LED Light
Input Voltage	24 VDC/VAC	Line Frequency	60 Hz
Indoor/Outdoor	Indoor	Sensor Coverage	120 ft
Mounting Type	Industrial Bracket, J-Box, Surface, Swivel Bracket	On Function	Auto On
Current Draw	8 mA	Sensing Range	10 x 134 ft
Wire Connection Type	Flying Leads	Voltage	24 VDC