



Wattstopper
0-10V Dual Tech. Wall Switch Occ. Sensor, 120/277V, Black
Part No. DW-311-B



The DW-311 dual technology dimming wall switch sensor can turn lights OFF and ON based on occupancy and allow the user to increase or decrease the lighting level. It combines the benefits of passive infrared (PIR) and ultrasonic occupancy detection technologies and works with 0-10 VDC dimming drivers and ballasts to control lighting loads including LEDs.

Features & Benefits

Collection consolidated of in 347 V to white option	Defaults to Manual-ON operation for maximum energy savings
High sensitivity and dense coverage for exceptional performance	Color-matched lens and low profile for appealing design
Supports Partial-ON operation for energy code compliance or incentives	120/277VAC and 347VAC models
Allows fully functional multi-way control from up to four switch locations	

Specifications

General Info

Product Line	Wattstopper	Color	Black
Finish	Glossy	UPC Number	754182939374
Country Of Origin	China	Product Series	DW-311
Features	Adjustable Time Delay, High/Low Trim, Indicator Lights, Light Level Sensor, Sensitivity Adjustment, Test Mode, Walkthrough Mode	Switch Type	Motion Sensor, Push
Installation Location	Wall	Included	Sensor Mask
Application Sector	Commercial	Standard	UL, cUL, E101196, UL 924, RoHS

Warranty Type	5-Year	Type	Sensor, Switch
Dimensions			
Product Width US	1.8 in	Product Weight US	0.3 lb
Product Volume US	35.1 cu in	Product Depth US	1.8 in
Product Height US	4.1 in		
Additional Information			
RoHS Compliant	Yes	Product Environmental Profile	Yes
Technical Information			
Operating Temperature Min	32 °F	Timer Type	DIP Switch
Load Rating	1000 W @ 120 VAC, 1200 W @ 230/240/277 VAC	Ultrasonic Frequency	40 kHz
Has Battery	No	Sensor Coverage Pattern	180 deg
Sensor Type	Occupancy	Operating Temperature Max	131 °F
Sensor Mounting Height	4 ft	Number of Buttons	2
Number of Rockers	0	Sensor Technology	Dual Technology, Passive Infrared (PIR), Ultrasonic
Timer Duration	5 Minutes, 15 Minutes, 30 Minutes	Number of Poles	Multi-Location
Indicator	PIR Detection LED, Selectable audible alert for impending shutoff, Ultrasonic Detection LED	Input Voltage	120/230/240/277 VAC
Requires Neutral Wire	No	Line Frequency	50 Hz, 60 Hz
Indoor/Outdoor	Indoor	Mounting Type	In-Wall
On Function	Selectable Auto/Manual	Operating Temperature	0°-55°C, 32°-131°F

Operating Humidity	5-95% RH (Non-Condensing)	Sensing Range	Major motion: PIR 35 x 30 ft, Ultrasonic 20 x 20 ft, Minor motion: PIR 20 x 15 ft, Ultrasonic 15 x 15 ft
Wire Connection Type	Flying Leads	Engraving Type	Icon
Storage Temperature	23° - 176° F, -5° - 80° C		