



Wattstopper 0-10V Dual Tech. Wall Switch Occ. Sensor, 120/277V, Black Part No. DW-311-B



The DW-311 dual technology dimming wall switch sensor can turn lights OFF and ON based on occupancy and allow the user to increase or decrease the lighting level. It combines the benefits of passive infrared (PIR) and ultrasonic occupancy detection technologies and works with 0-10 VDC dimming drivers and ballasts to control lighting loads including LEDs.

Features & Benefits

Defaults to Manual-ON operation for maximum energy savings

High sensitivity and dense coverage for exceptional performance

Color-matched lens and low profile for appealing design

Supports Partial-ON operation for energy code compliance or incentives

120/277VAC and 347VAC models

Allows fully functional multi-way control from up to four switch locations

Specifications

General Info

Product Line	Wattstopper	Color	Black
UPC Number	754182939374	Country Of Origin	China
Features	IR (Infrared), Motion Sensor	Switch Type	Motion Sensor
Application Sector	Commercial		

Dimensions

Product Width US	3.0 in	Product Weight US	0.5 lb
Product Volume US	37.5 cu in	Product Depth US	5.0 in
Product Height US	2.5 in		

Additional Information

RoHS Conformant	Yes	DesignLights Consortium Qualified System	Yes
-----------------	-----	--	-----

Security	Yes	Product Environmental Profile	Yes
----------	-----	-------------------------------	-----

Technical Information

Response Frequency	50/60 Hz	Sensor Type	Occupancy
--------------------	----------	-------------	-----------

Number of Buttons	3	Amperage	8.3 A
-------------------	---	----------	-------

Wattage	1200 W	Mounting Type	Box
---------	--------	---------------	-----

Sensing Range	180 degrees, 1050 sq ft	Voltage	120/277 V
---------------	-------------------------	---------	-----------

Connection Type	Wired	Load	1000W
-----------------	-------	------	-------
