On-Q
9-inch Dual-Purpose In-Wall Enclosure
Part No. ENP0900NA



The 9-inch Dual-Purpose In-Wall Enclosure is engineered to provide storage of structured wiring and AV components. The ENP0900NA is constructed of Wi-Fi transparent material to manage wireless components and AV devices at point-of-use locations, like directly behind a TV or other media centers. It can also be used for structured wiring purposes, such as networking equipment, access points, switches and more. The ENP0900NA is compatible with devices like Apple TV, Roku, Amazon Fire TV, small network switches and more. Includes cover, trim ring and drywall clips, allowing for both new construction and retrofit installations.

Features & Benefits

- Designed for in-wall storage and distribution of structured wiring and AV components
- Can be placed behind most TV wall-mounts including SANUS premium TV mounts
- Compatible with devices like Apple TV, Roku, Amazon Fire TV, network switches, 3rd party structured wiring components and more
- Trim ring conceals drywall cut out for clean finish and smooth transition to wall surface
- Tool-free cover is low profile and designed to snap into place providing a "flush" appearance to wall surface
- Knockout configurations support conduit and in-wall wired connections, while a cable pass through on cover allows for outside cable connections
- Features (2) AC knockouts to accommodate a single gang junction box to power devices in enclosure
- Universal mounting grid maximizes compatibility with 3rd party devices without additional mounting brackets
- Features drywall clips to allow both retrofit and new construction installations
- UL Listed and constructed of Wi-Fi transparent ABS plastic to ensure uninterrupted performance of wireless devices
- Proudly made in the USA

Specifications

General Info

Product Line	On-Q	Color	White
Finish	Matte	UPC Number	804428434542
Country Of Origin	United States	Package Quantity	1
Application Sector	Residential/Commercial	Standard	RoHS, UL, cULus
Type	Enclosure		

Dimensions

Product Width US	14.37 in	Product Depth US	3.88 in
Product Height US	9.33 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes

Additional Information

RoHS Conformant	Yes

Technical Information

Compatibility	Paintable with Rust-Oleum paint for plastic or equivalent	Thickness	0.1 in
Enclosure Type	Dual Purpose	Frame	Injection-molded plastic
Operating Temperature	32°-122°F	Mounting	Consult the Factory for Mounting Recommendations
Environmental Conditions	0 to 93% (relative humidity, non-condensing)		