



Wattstopper
0-10V PIR STRAIGHT MT SENSOR BLE 120-480V 10FT LENS -GREY
Part No. FSP-321B-S-L2-G



The FSP-3x1B sensors provide continuous dimming light level control based on motion and/or daylight contribution. They control 0-10 VDC LED drivers or dimming ballasts, as well as non-dimming ballasts and, with an FSP-Lx Lens, are rated for wet and cold locations. All control parameters are adjustable via the iOS or Android Sensor Configuration App capable of storing and transmitting sensor profiles. The FSP-3x1B family is available in three configurations for mounting inside a fixture, to the outside of a fixture via a 1/2" knockout, or to a pole.

Features & Benefits

Designed for LED fixtures and rated for extreme temperatures; options for box or pole mounting

Fully adjustable high and low dimmed light levels

Hold off setpoint with automatic calibration option for convenience and added energy savings

Continuous dimming & daylight harvesting for energy efficiency and energy code compliance

Adjustable via the iOS® or Android® Sensor Configuration App

IP66 rated with choice of lenses for wet and outdoor locations, and mounting heights from 8' to 40'

Adjustable time delay and cutoff delay

Specifications

General Info

| | | | |
|--------------|--------------|-------------------|-------|
| Product Line | Wattstopper | Color | Gray |
| UPC Number | 754182941612 | Country Of Origin | China |

Dimensions

| | | | |
|-------------------|-------------|-------------------|---------|
| Product Width US | 6.0 in | Product Weight US | 0.44 lb |
| Product Volume US | 39.69 cu in | Product Depth US | 6.3 in |
| Product Height US | 1.0 in | | |

Technical Information

| | |
|-------------|---------------------|
| Sensor Type | Daylight, Occupancy |
|-------------|---------------------|