




Ortronics
Infinium M4 HDFP Adapter Panel, 8 Keyed Front Non-Keyed Rear LC Duplex Adapters, 16 Fibers, Black
Part No. HDFP-LCD16YC-U

Legrand keyed LC fiber adapter panels are available in configurations that are keyed on the front only or on both sides. The adapter panels are designed to fit Legrand Infinium HD rack mount enclosures. Up to thirteen key colors of connectors are possible with unique physical keying configurations.



Features & Benefits

- Unique Key and Color Options: Up to thirteen unique keying options/colors for a wide range of network security systems, easy identification and network management.
- Various Footprint Options: Keyed workstation adapter modules are available for TracJack® and High Density Jack (HDJ) style Face plates and surface mount boxes for complete system design flexibility.
- Keyed front or Rear: Keyed LC adapters have the option to be keyed in the front only (user's side) or on both sides (user's and technician's) depending on the security requirements. Internal keying feature prevents tampering
- Compatibility: All Legrand keyed LC fiber products are engineered to be compatible with other Legrand products to provide an end to end, data center to desktop solution.

Specifications

General Info

Product Line	Ortronics	Color	Black
UPC Number	662875030447	Country Of Origin	Mexico
Features	Keyed Connector	Included	Cover
Application Sector	Commercial, Data Center	Standard	RoHS compliant. Meets or exceeds TIA/EIA-568-C.3 requirements
Warranty Type	5-Year	Type	Adapter Panel

Dimensions

Product Width US	4.19 in	Product Depth US	0.66 in
Product Height US	1.24 in		

Technical Information

Fiber Optic Cable Type	OM3, OM4, OS2	Operating Temperature Min	-10 °C
Compatibility	HDFP	Number of Ports	16
Simplex/Duplex	Duplex	Operating Temperature Max	60 °C
Shuttered Adapters	No	Number of Fibers	16 Fibers
Connector 2	Keyed	Connector 1	Keyed

Operating Temperature

-10°-60°C

Operating Humidity

0-80% RH (Non-Condensing)