



**On-Q**  
**In-Wall Power & Cable Management TV Connection Kit - New Construction/Retrofit (Canadian Compliant)**  
Part No. HT2302CWH



**HT2302C-WH**  
INCLUDES BOX WITH TRIM RING AND JUNCTION BOX  
(CANADA COMPLIANT)

The Recessed TV Box for power and low voltage supports power and class 2 low voltage behind a wall mounted TV. The design allows for cables and power connections to be tucked away, allowing TVs to be flush against the wall. The box can be mounted directly to a wall stud in new construction or use the wing clamps to secure to drywall in a retrofit applications. The recessed TV Box fits in a standard 2x4 wall, and supports wall thicknesses up to 1in. The Class 2 Low voltage side includes concentric knockout rings to support flexible conduit connections. Product contents include: Recessed TV Box, Removable Trim Ring, 1 Gang Old-Work Junction Box with grounding strap, and necessary mounting hardware.

## Features & Benefits

Provide recessed power and AV connectivity support for a wall mounted TV.

Recessed TV box mounts directly to wall studs with included screws for new construction and retrofit installation

Hides both power and AV cables inside the wall for a clean, professional installation

The Low voltage side of the box includes concentric knockout rings for support of flexible conduit connections.

Recessed TV box includes pre-installed wing clamps to secure to drywall in retrofit installations.

Kit Contents Include: Recessed TV Box, Removable Trim Ring, 1 Gang Old-Work Junction Box with grounding strap, and necessary mounting hardware.

## Specifications

### General Info

Product Line	On-Q	Color	White
Finish	Glossy	UPC Number	804428435082
Country Of Origin	China	Application Sector	Residential
Standard	cUL	Warranty Type	5-Year
Type	Wall Box		

### Dimensions

Product Width US	3.8 in	Product Weight US	0.82 lb
Product Height US	8.7 in	Product Length US	8.37 in

### Listing Agencies / 3rd Party Agencies

cUL Listed	Yes
------------	-----

### Technical Information

Is Tamper-Resistant	No	Temperature Rating	32° - 122° F
Is Weather Resistant	No	Indoor/Outdoor	Indoor
Voltage	125.0 V		