



6' Plugmold Multioutlet System with 6 single outlets

## Features & Benefits

Steel Raceway. Provides superior strength for any dry location installation.

Available in Ivory ScuffCoat or gray baked enamel finish. The durable ScuffCoat provides a durable, scratch-resistant finish while the gray baked enamel compliments the décor or can be painted.

Single-and-dual-gang boxes. Wire devices into the raceway system or protect a Plugmold® strip with a surge or GFCI device.

Single, alternating circuit, and isolated ground receptacles. Meets virtually any job requirement.

Snapicoil harnesses of prewired receptacles in 48' and 50'. Eliminates multiple splicing, speeding up installation on long runs.

Customization available. All products can be modified to accommodate virtually any application.

Compact, low profile appearance. Requires minimal space.

Full range of fittings. Provides a complete wiring solution.

Factory wired Plugmold® sections available in 3', 5', and 6' lengths with 15A receptacles installed in cover. Ideal for short runs requiring additional outlets in electrically busy areas.

Choice of receptacle spacing. Center spacing between receptacles of 6", 9", 12", and 18".

Snapicoil harnesses offer a choice of receptacle spacing. Center spacing between receptacles of 12", 18" and 30".

This product meets the material restrictions of RoHS.

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786776096804
Country Of Origin	United States	Number of Receptacles	6

Application Sector	Commercial	Standard	cULus Listed Base & Blank Cover: File E4376 Guide RJBT. Multioutlet Assemblies: File E15191 Guide PVGT. Fittings: File E41751 Guide RJPR. Base & Blank Cover & Plugmold Series w/Snapicoil Haarness: Meets Article 386 of NEC. Meets Section 12-3032 of CEC. cULus Listed Raceway: File E4376 Guide RJBT. Fittings: File E41751 Guide RJPR. Base & Black Cover: Meets Article 386 of NEC. Meets Section 12-600 of CEC.
Type	Plugmold		
Dimensions			
Product Width US	1.3 in	Product Weight US	3.95 lb
Product Depth US	0.75 in	Product Length US	1.3 in
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E15191	cULus Listed	Yes
Additional Information			
RoHS Compliant	Yes	Product Environmental Profile	Yes
Technical Information			
Amperage	15 A	Enclosure Type	Steel
Voltage	125.0 V	Environmental Conditions	Dry interior locations