



Pass and Seymour

Isolated Ground Heavy Duty Spec Grade Single Receptacles, Back and Side Wire, 15A, 125V, Orange

Part No. IG5261

Isolated Ground Heavy-Duty Spec Grade Single Receptacle Back and Side-Wire 15A 125V



Features & Benefits

IG symbol and Isolated Ground markings for easy identification and circuit delineation.

High-impact resistant nylon face resists impacts and scrapes.

Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

Side and internal screw-pressure-plate back wire capability with #14 - #10 AWG copper or copper-clad, solid or stranded wire.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.

Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Triple-wipe brass contacts ensure lasting, positive contact with plug blades.

Corrosion-resistant plated steel strap.

Plastic barrier isolates grounding terminal from mounting strap and metal boxes.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Orange
UPC Number	785007652611	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL498, CSA C22.2 No. 42, FEDSPEC

Dimensions

Product Width US	1.32 in	Product Depth US	1.093 in
Product Height US	1.68 in		

Listing Agencies / 3rd Party Agencies

cUL ListingNumber	140596	cUL Listed	Yes
-------------------	--------	------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
Number of Wires	3	Temperature Rating	-40° - 60° C
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Environmental Conditions	Flammability: UL94 V2