



Isolated Ground Heavy-Duty Spec Grade Duplex Receptacle Back and Side Wire 15A 125V

### Features & Benefits

IG symbol and Isolated Ground markings for easy identification and circuit delineation.	Face color coding by voltage facilitates locating and mating of proper devices.
High-impact resistant nylon face resists impacts and scrapes.	Corrosion-resistant plated steel strap.
Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.	Plastic barrier isolates grounding terminal from mounting strap and metal boxes.
Auto-ground clip assures positive ground.	For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .
For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, <a href="#">click here</a> .	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

### Specifications

#### General Info

Product Line	Pass & Seymour	UPC Number	785007045307
Country Of Origin	United States	Number of Receptacles	2
Application Sector	Commercial	Standard	UL498, CSA C22.2 No. 42, FEDSPEC
Type	Outlet		

#### Dimensions

Product Width US	1.322 in	Product Depth US	0.922 in
Product Height US	2.635 in		

#### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

---

### Technical Information

Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
Number of Wires	3	Temperature Rating	-40° - 60° C
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
Environmental Conditions	Flammability: UL94 V2		

---