



Shielded Clarity High Density Jacks incorporate mechanical and electrical advancements to provide industry leading protection against EMI, with electrical and data transmission performance headroom, and a simple termination method. The easy to lace and crimp termination reduces time to install, while maintaining cable performance. These jacks are rear loading, utilizing an innovative locking latch for quick reliable mounting and removal.

Features & Benefits

- Circuit traces: Each circuit trace is rated to 100W, 1.5A
- Enhances PoE heat dissipation: Ideal for high-power PoE applications
- Versatile mounting: Use at both ends of the channel, compatible with patch panels, wall plates, furniture plates, surface mount boxes and more
- Rear loading: Preferred mounting for panels
- Lacing Cap Design: No punch tool required, quick termination and installation time.
- Enhanced ergonomics: Optional high durability metal, lacing cap termination tool makes install easier, improving bulk installation and sustainability. Part Number: HDJHCT
- Superior Protection Against EMI: Minimizes disturbances in data transmission
- Accepts color ID icons: Perfect for port identification or segmentation
- High density footprint: Mount up to 48 ports per 1RU
- Plenum Rated to UL 2043: Can be installed in any air handling space
- Always Ready for Install: Each package of jacks includes 1 standard lacing cap termination tool (Compatible with any HDJ or KT2 jacks).
- Replacement plastic lacing cap termination tools, part number: HDJPCT-4PK

Specifications

General Info

Product Line	Ortronics	UPC Number	662875020066
Country Of Origin	Mexico	Application Sector	Commercial, Industrial
Standard	UL Standard	Type	Jack

Dimensions

Product Width US	0.63 in	Product Depth US	1.61 in
------------------	---------	------------------	---------

Product Height US	0.77 in
-------------------	---------

Additional Information

RoHS Compliant	Yes
----------------	-----
