



On-Q
In-Wall Power & Cable Management TV Connection Kit - New Construction/Retrofit (with outlet)
Part No. HT2302KWH



Enhance your TV setup with the In-Wall Power & Cable Management TV Connection Kit, featuring a tamper-resistant outlet. Suitable for both new construction and retrofit applications, this kit supports power and Class 2 low voltage behind a wall-mounted TV. The recessed design keeps cables and power connections hidden, allowing your TV to sit flush against the wall. The box can be mounted directly to a wall stud or secured to drywall using wing clamps. It fits in a standard 2x4 wall and supports wall thicknesses up to 1 inch. The Class 2 low voltage side includes concentric knockout rings for flexible conduit connections. Product contents include: Recessed TV Box, Removable Trim Ring, 1 Gang Old-Work Junction Box, Tamper-Resistant Outlet, Cable Access Brush Strap, Wall Plates, and necessary mounting hardware.

Features & Benefits

- Provide recessed power and AV connectivity support

Tamper Resistant receptacle powers multiple devices such as a TV, sound bar or streaming players
- The Low voltage side of the box includes concentric knockout rings for support of flexible conduit connections.

Recessed TV box mounts directly to wall studs with included screws for new construction installation
- Hides both power and AV cables inside the wall for a clean, professional installation

Kit Contents Include: Recessed TV Box, Removable Trim Ring, 1 Gang Old-Work Junction Box, Tamper resistant outlet, cable access brush strap, wall plates, and necessary mounting hardware.

Specifications

General Info

Product Line	On-Q	Color	White
Finish	Glossy	UPC Number	804428435099
Country Of Origin	China	Receptacle Type	5-15R
Number of Receptacles	1	Application Sector	Residential
Standard	ULus	Warranty Type	5-Year
Type	Outlet, Wall Box		

Dimensions

Product Width US	3.8 in	Product Weight US	1.12 lb
Product Height US	8.7 in	Product Length US	8.37 in

Technical Information

Is Tamper-Resistant	No	Number of Gangs	1
---------------------	----	-----------------	---

Temperature Rating	32° - 122° F	Number of Poles	3-Way
Is Weather Resistant	No	Requires Neutral Wire	Yes
Indoor/Outdoor	Indoor	Voltage	125.0 V