



Isolated Ground Heavy-Duty Decorator Hospital Grade Duplex Receptacle Back and Side-Wire 15A 125V



## Features & Benefits

IG symbol and Isolated Ground markings for easy identification and circuit delineation.

High-impact resistant nylon face resists impacts and scrapes.

Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

Side and internal screw-pressure-plate back wire capability with #14 - #10 AWG copper or copper-clad, solid or stranded wire.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Triple-wipe brass contacts ensure lasting, positive contact with plug blades.

Corrosion-resistant plated steel strap.

Plastic barrier isolates grounding terminal from mounting strap and metal boxes.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Orange
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL498, CSA C22.2 No. 42		

### Dimensions

Product Width US	1.322 in	Product Depth US	0.833 in
------------------	----------	------------------	----------

---

Product Height US 2.635 in

---

**Listing Agencies / 3rd Party Agencies**

---

cULus ListingNumber 140596 cULus Listed Yes

---

**Technical Information**

---

Dielectric Strength Withstands 2000V minimum Connection Back and side wire

---

Number of Wires 3 Temperature Rating -40° - 60° C

---

Amperage 15 A Number of Poles Double Pole

---

Wire Size 14 - 10 AWG Voltage 125.0 V

---

Environmental Conditions Flammability: UL94 V2

---