



Pass and Seymour
20A 125V Isolated Ground Surge Protective Duplex Receptacle, Back and Side Wire, Light Almond
Part No. IG5362LASP



Isolated Ground Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). Back and Side Wire, 20A, 125V

Features & Benefits

Solid-state LED monitor has 25-year minimum life expectancy. A high visibility, wide-angle lens indicates protection is in place.

Audible alarm alert of MOV damage. Alarm able to be turned On/Off.

Triple-wipe, copper-alloy contacts for superior, more dependable connection.

External pressure plate feature allows two conductors to be terminated by a single screw.

For covering patents, see www.legrand.us/patents.

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Wrap-around steel strap for structural integrity. Auto-ground is standard, for easier installation.

External screw-pressure-plate back and side wire terminals including ground with external back wire clamps (exclusive) accept #14 - #10 AWG copper or copper-clad, solid or stranded conductors.

Plastic barrier isolates grounding terminal from mounting strap and metal boxes.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007194579
Country Of Origin	Mexico	Application Sector	Commercial
Standard	cUL UL1449, UL498: CSA C22.2 No. 42: ANSI/EEE C62.41 (Formerly IEEE 587), ANSI/IEEE C62.45 Installation Categories "A" (Ring Wave) "B" (Unidirectional Impulse).		

Dimensions

Product Width US	1.75 in	Product Depth US	1.225 in
Product Height US	2.8 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
Technical Information			
Connection	Back and side wire	Class	IG
Amperage	20 A	Environmental Conditions	Flammability: UL94 V2