



Isolated Ground Heavy-Duty Spec Grade Duplex Receptacle Back and Side-Wire 15A 250V

Features & Benefits

- IG symbol and Isolated Ground markings for easy identification and circuit delineation.
- High-impact resistant nylon face resists impacts and scrapes.
- Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
- Side and internal screw-pressure-plate back wire capability with #14 - #10 AWG copper or copper-clad, solid or stranded wire.
- For covering patents, see www.legrand.us/patents.
- Triple-wipe brass contacts ensure lasting, positive contact with plug blades.
- Corrosion-resistant plated steel strap.
- Plastic barrier isolates grounding terminal from mounting strap and metal boxes.
- Auto-ground clip assures positive ground.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Orange
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL498, CSA C22.2 No. 42		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
Technical Information			
Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
Number of Wires	3	Temperature Rating	-40° - 60° C
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Voltage	250 V
Environmental Conditions	Flammability: UL94 V2		