



Isolated Ground Heavy-Duty Decorator Hospital Grade Duplex Receptacle Back and Side-Wire 15A 125V

Features & Benefits

IG symbol and Isolated Ground markings for easy identification and circuit delineation.

High-impact resistant nylon face resists impacts and scrapes.

Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

Side and internal screw-pressure-plate back wire capability with #14 - #10 AWG copper or copper-clad, solid or stranded wire.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Triple-wipe brass contacts ensure lasting, positive contact with plug blades.

Corrosion-resistant plated steel strap.

Plastic barrier isolates grounding terminal from mounting strap and metal boxes.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

| | | | |
|-------------------|-------------------------|--------------------|------------|
| Product Line | Pass & Seymour | Color | White |
| Country Of Origin | Mexico | Application Sector | Commercial |
| Standard | UL498, CSA C22.2 No. 42 | | |

Dimensions

| | | | |
|------------------|----------|------------------|----------|
| Product Width US | 1.322 in | Product Depth US | 0.833 in |
|------------------|----------|------------------|----------|

| | |
|-------------------|----------|
| Product Height US | 2.635 in |
|-------------------|----------|

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

| | | | |
|---------------------|--------------------------|------------|--------------------|
| Dielectric Strength | Withstands 2000V minimum | Connection | Back and side wire |
|---------------------|--------------------------|------------|--------------------|

| | | | |
|-----------------|---|--------------------|--------------|
| Number of Wires | 3 | Temperature Rating | -40° - 60° C |
|-----------------|---|--------------------|--------------|

| | | | |
|----------|------|-----------------|-------------|
| Amperage | 15 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

| | | | |
|-----------|-------------|---------|---------|
| Wire Size | 14 - 10 AWG | Voltage | 125.0 V |
|-----------|-------------|---------|---------|

| | |
|--------------------------|-----------------------|
| Environmental Conditions | Flammability: UL94 V2 |
|--------------------------|-----------------------|
