



Pass and Seymour
Isolated Ground Heavy Duty Hospital Grade Receptacles, Back and Side Wire, 15A, 125V, Red
Part No. IG8200RED



Isolated Ground Heavy-Duty Hospital Grade Duplex Receptacle, Back and Side Wire, 15amp 125volt, Ivory.

Features & Benefits

IG symbol and Isolated Ground markings for easy identification and circuit delineation.

High-impact resistant nylon face resists impacts and scrapes.

Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

Side and internal screw-pressure-plate back wire capability with #14 - #10 AWG copper or copper-clad, solid or stranded wire.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.

Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Triple-wipe brass contacts ensure lasting, positive contact with plug blades.

Corrosion-resistant plated steel strap.

Plastic barrier isolates grounding terminal from mounting strap and metal boxes.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
UPC Number	785007820461	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL498, CSA C22.2 No. 42, FEDSPEC

Dimensions

Product Width US	1.322 in	Product Depth US	0.922 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
Number of Wires	3	Temperature Rating	-40° - 60° C
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Environmental Conditions	Flammability: UL94 V2