

Turnlok Single Receptacle 5wire 30amp 3phase 120/208volt Isolated Ground



Features & Benefits

UL1449 (latest revision), (1.2 x 50: s 6000V, 8 x 20: s 3000A).

9,000 amps current handling capability in each of three modes: line to neutral, line to ground, neutral to ground.

Nominal let-through (suppressed) voltage in all 3 modes, 500V.

Response time less than 1 nanosecond for unmounted MOV.

Electronic components potted for electrical, mechanical and thermal stability.

Leakage current: 0.5 mA at 25: C/120VAC.

Common mode noise attenuation: 500 KHz to 30 MHz: up to 35 dB (50 ohm source impedance)

Back and side wire capability including ground terminal.

Conforms to the latest revision ANSI/IEEE C62.41 (formerly IEEE 587), ANSI/IEEE C62.45.

140 joules of energy absorption in each of the three modes.

1 filtering capacitor for 7 to 1 average noise reduction.

LED indicator light.

Overcurrent protection in all 3 modes.

Thermal protection in all 3 modes.

3 18mm super MOVs to suppress transients in all modes : equally.

Varistor voltage: 150V RMS.

Operating temperature: -40: C to 85: C (-40: F to 185: F)

Specifications

General Info

Color	Orange	UPC Number	785007213065
-------	--------	------------	--------------

Country Of Origin	Mexico	Product Line	Pass & Seymour
-------------------	--------	--------------	----------------

Application Sector	Commercial	Standard	UL 498
--------------------	------------	----------	--------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	140596
--------------	-----	---------------------	--------

Technical Information

Number of Poles	3-Way	Voltage	120 V
-----------------	-------	---------	-------

Phase	3	Wire Size	10-18Awg
-------	---	-----------	----------

Number of Wires	4
-----------------	---