



**Wiremold**  
**deQuorum Cord-Ended Unit**  
 Part No. KC15RT8



Cord-ended with gray, flush cover. Unit comes with two 20A gasketed prewired receptacles with a 12' (3.65m) 14/3 SJT black cord. Includes adapter for Ortronics Series II and TracJack inserts. Communication modules sold separately.

## Features & Benefits

- Hinged lid. Provides access to make connections and can be closed during use making the portal unobtrusive. Finish options. Choose the finish of the flip-top lid.
- Cover options. Choose either flush or contoured. Both options are available with a decorative, recessed area that can accept a wide range of laminates and veneers. Configurable. Choose the communications requirements from the latest UTP to video and fiber optics.
- Datacom connectivity options. Accepts industry standard and proprietary devices from a wide range of manufacturers to provide a seamless and aesthetically pleasing interface for voice, data, audio, and video applications at the point of use Gasketed Receptacle. 15A spec grade receptacle is dust and moisture resistant.\*
- Installation flexibility. Unit is plug-ended or field-installable. Flush. When closed, the unit does not interfere with the worksurface.
- Listed to U.S. and Canadian safety standards.

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786776161199
Country Of Origin	United States	Construction	Aluminum
Application Sector	Commercial	Standard	cULus Listed Relocatable Power Tap: File E66421 Guide XYBS, cULus Listed Multioutlet Assembly: File E15191 Guide PVGT, Meets Article 380 of NEC
Type	Table Box		

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

---

### Buy American Act Compliance

---

NAFTA	Yes
-------	-----

---

### Additional Information

---

RoHS Conformant	Yes
-----------------	-----

---

### Technical Information

---

Mounting Type	Recessed	Number of Outlets	2
---------------	----------	-------------------	---

---