

Turnlok® Single Receptacle 4-Wire 20A 3-Phase 480V Isolated Ground



## Features & Benefits

UL1449 (latest revision). (1.2 x 50: s 6000V, 8 x 20: s 3000A). 140 joules of energy absorption in each of the three modes.

9,000 amps current handling capability in each of three modes: line to neutral, line to ground, neutral to ground. 1 filtering capacitor for 7 to 1 average noise reduction.

Nominal let-through (suppressed) voltage in all 3 modes, 500V. LED indicator light. Response time less than 1 nanosecond for unmounted MOV.

Overcurrent protection in all 3 modes. Electronic components potted for electrical, mechanical and thermal stability.

Thermal protection in all 3 modes. Leakage current: 0.5 mA at 25: C/120VAC.

3 18mm super MOVs to suppress transients in all modes : equally. Common mode noise attenuation: 500 KHz to 30 MHz: up to 35 dB (50 ohm source impedance) Varistor voltage: 150V RMS. Back and side wire capability including ground terminal.

Operating temperature: -40: C to 85: C (-40: F to 185: F) Conforms to the latest revision ANSI/IEEE C62.41 (formerly IEEE 587), ANSI/IEEE C62.45.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Orange
UPC Number	785007162103	Country Of Origin	Mexico
Application Sector	Industrial	Standard	UL Listed

---

Dimensions

---

Product Width US	1.61 in	Product Depth US	1.19 in
------------------	---------	------------------	---------

---

Product Height US	2.29 in		
-------------------	---------	--	--

---

Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

---

Technical Information

---

Phase	Three	Number of Wires	4
-------	-------	-----------------	---

---

Amperage	20 A	Number of Poles	3-Way
----------	------	-----------------	-------

---