



Industrial Spec Grade SingleTurnlok® 20A 480V Receptacle

## Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

## Specifications

### General Info

|                    |                |                   |                         |
|--------------------|----------------|-------------------|-------------------------|
| Product Line       | Pass & Seymour | Country Of Origin | Mexico                  |
| Application Sector | Industrial     | Standard          | UL498, CSA C22.2 No. 42 |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 1.61 in | Product Depth US | 1.19 in |
| Product Height US | 2.29 in |                  |         |

### Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

---

Additional Information

---

Product Environmental Profile    Yes

---

Technical Information

---

|                          |                                                                                                      |                 |             |
|--------------------------|------------------------------------------------------------------------------------------------------|-----------------|-------------|
| Connection               | Back and side wire                                                                                   | Number of Wires | 3           |
| Amperage                 | 20 A                                                                                                 | Number of Poles | Double Pole |
| Wire Size                | 14 - 10 AWG                                                                                          | Voltage         | 480.0 V     |
| Environmental Conditions | Flammability: UL94 V2: Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact |                 |             |

---