



Receptacle Single 4-Wire 30A 347/600V Turnlok®

## Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

## Specifications

### General Info

|                   |                |                    |            |
|-------------------|----------------|--------------------|------------|
| Product Line      | Pass & Seymour | Color              | Black      |
| Country Of Origin | Mexico         | Application Sector | Commercial |
| Standard          | UL 498         |                    |            |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 1.61 in | Product Depth US | 1.28 in |
| Product Height US | 2.37 in |                  |         |

### Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

---

Additional Information

---

|                               |     |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

---

Technical Information

---

|           |             |                 |         |
|-----------|-------------|-----------------|---------|
| Phase     | 3           | Number of Wires | 4       |
| Amperage  | 30 A        | Number of Poles | 4-Way   |
| Wire Size | 18 - 10 AWG | Voltage         | 600.0 V |

---