



**Wattstopper**  
**Discontinued - Digital Dimming Wall Switch, 1 paddle, w/IR, Ivory**  
Part No. LMDM-101-I



The LMDM-101 Digital Dimming Wall Switch is a low voltage device for dimming control of one or more lighting loads. It is part of a Digital Lighting Management (DLM) system and can dim load(s) connected to DLM dimming room controllers and switch load(s) connected to DLM on/off room controllers.

## Features & Benefits

- Low voltage switch for control of dimmable loads Plugs to other components using Cat 5e cable and RJ45 connectors eliminating wiring errors
- LED bar graph indicates relative light level of controlled load Active Dim feature enables temporary adjustment of any selected load
- IR transceiver for wireless configuration and remote control

## Specifications

### General Info

Product Line	Wattstopper	Color	Ivory
UPC Number	754182929252	Country Of Origin	China
Material	ABS	Product Series	LMDM
Switch Type	Push	Number of Switches	1
Application Sector	Commercial	Warranty Type	5-Year
Type	Dimmer, Switch		

### Dimensions

Product Width US	1.8 in	Product Weight US	0.2 lb
Product Volume US	11.8 cu in	Product Depth US	1.6 in

---

Product Height US	4.1 in
-------------------	--------

---

### Additional Information

---

RoHS Compliant	Yes	Security	Yes
----------------	-----	----------	-----

---

### Technical Information

---

Operating Temperature Min	0 °C	Compatibility	DLM Wired
---------------------------	------	---------------	-----------

---

Has Battery	No	Number of Connections	2
-------------	----	-----------------------	---

---

Operating Temperature Max	55 °C	Number of Buttons	1
---------------------------	-------	-------------------	---

---

Number of Rockers	0	Input Voltage	24 VDC
-------------------	---	---------------	--------

---

Indoor/Outdoor	Indoor	Mounting Type	J-Box
----------------	--------	---------------	-------

---

Current Draw	5 mA	Operating Temperature	0°-55°C, 32°-131°F
--------------	------	-----------------------	--------------------

---

Operating Humidity	5-95% RH (Non-Condensing)	Location Rating	Dry
--------------------	---------------------------	-----------------	-----

---

Wire Connection Type	RJ-45	Engraving Type	Blank
----------------------	-------	----------------	-------

---