



Heavy-Duty Ground Continuity Monitoring (GCM) Connector, Black and White



Features & Benefits

Integral indication of ground continuity and power status. Continuous monitoring enhances personnel safety and adds convenience.

For 250V configurations: Hot to ground cross will be indicated by a green and red LED.

Exclusive neoprene dust shield on devices seals cable entry. Optional weatherproof boots (sold separately).

Exclusive, rugged two-piece cord grip (15 Amp only) accepts a wide range of cord widths. Provides uniform pressure for superior retention of conductors.

Color-coded terminal screws are backed-out for fast installation.

Dual, bright LED indicators with 360 degrees visibility. Green LEDs indicate proper ground continuity and power status. Red LEDs indicate ground continuity loss or reversed polarity. No LED indicates open hot, open neutral, or hot to ground cross.

NEMA configurations always visible for fast identification without disconnecting.

Chemical- and impact-resistant nylon housing features horizontal, easy-grip ribs on back body.

Recessed cord-grip screw reduces screwdriver slippage, improves safety. Quick-thread tri-drive assembly and cord-grip screws come backed-out and ready-to-wire.

Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007265637	Country Of Origin	United States
Application Sector	Industrial	Standard	UL Listed, FEDSPEC

Dimensions

Product Width US	2.2 in	Product Length US	3.33 in
------------------	--------	-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Phase	Three	Number of Wires	3
Amperage	30 A	Number of Poles	Double Pole