



Turnlok® Single Receptacle, 3-Wire 20A 600V, L9-20R

Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

| | | | |
|--------------------|----------------|-------------------|--------|
| Product Line | Pass & Seymour | Country Of Origin | Mexico |
| Application Sector | Commercial | Standard | UL 498 |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 1.61 in | Product Depth US | 1.19 in |
| Product Height US | 2.29 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Additional Information

Product Environmental Profile Yes

Technical Information

| | | | |
|-------|---|-----------------|---|
| Phase | 3 | Number of Wires | 3 |
|-------|---|-----------------|---|

| | | | |
|----------|------|-----------------|-------------|
| Amperage | 20 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

| | | | |
|-----------|-------------|---------|---------|
| Wire Size | 18 - 10 AWG | Voltage | 600.0 V |
|-----------|-------------|---------|---------|
