



Ortronics

Infinium Quantum M4 Cassette - 25 Fiber - LC Quad to MPOM - OS2 - Universal Polarity

Part No. LM4-LC24J-2A3UN

..

No longer bound by Ultra Low Loss - Infinium Quantum has redefined performance in the data center with a total channel connection loss that is an order of magnitude greater than any other fiber system on the market today. Infinium quantum changes everything by opening up the opportunity to challenge what's possible.



Features & Benefits

- High Density: 12 or 24-fiber cassette compatible with Infinium HD M4 Enclosures
- Versatile Installation: Infinium Modular Panel enables mixed media installations
- Fiber Type: Supports either Single-mode OS2 or Multimode Infinium Ultra fiber
- Polarization: Universal
- LC adapter with internal shutter: Ensures eye safety by blocking laser light when the connector is removed. Automatic shutter requires no manual handling.
- Infinium Ultra: Ultra Low Loss System with Infinium Ultra Trunks and Patch Cords: Single-mode channel loss: 1.2 dB, return loss: 49 dB. Multimode channel loss: 1.0 dB, return loss: 19 dB.
- Compatible with LC connectors, keeps the interior clean, and allows visible light to pass through.
- Infinium Core: Low Loss System with Infinium Core Trunks and Patch Cords: Single-mode channel loss: 2.1 dB, return loss: 49 dB. Multimode channel loss: 2.5 dB, return loss: 19 dB.

Specifications

General Info

Product Line	Ortronics	Color	Blue
UPC Number	662875031192	Country Of Origin	Mexico
Application Sector	Commercial	Standard	TIA-568-C.3
Warranty Type	5-Year	Type	Cassette

Dimensions

Product Width US	4.24 in	Product Depth US	4.77 in
Product Height US	1.14 in		

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Fiber Optic Cable Type	OS2	Compatibility	HDFP, LM4
Number of Ports	24	Simplex/Duplex	Duplex
Single/Multimode	Single-Mode	Performance Level/Tier	Infinium Quantum
