



The LMJA-8xxx-SM is a Network Controller designed to communicate with Wired and Wireless DLM Network Bridges, for local in-room wired networks and/or LMCP panels. It provides control, monitoring, adjustment, and standard or Human Centric Lighting (HCL) scheduling functionality for networked DLM systems. The Network Supervisor is a PC server running similar software designed to coordinate control of multiple LMJA-8xxx-SMs and store historical data

Features & Benefits

- Provides global control of DLM segment networks and access to advanced features
- Support for both Wired and Wireless DLM network Bridges
- Runs Niagara N4.9 with DLM Segment Manager Station
- Designed for and supports third party integration with BAS through BACnet/IP

Specifications

General Info

Product Line	Wattstopper	Color	Black
UPC Number	754182944743	Country Of Origin	United States
Product Series	LMJA	Installation Location	Wall
Application Sector	Commercial	Standard	UL 916, RoHS, FCC part 15
Warranty Type	1-Year	Type	Expansion Module

Dimensions

Product Width US	2.4 in	Product Weight US	0.3 lb
Product Volume US	25.9 cu in	Product Depth US	2.4 in
Product Height US	4.5 in		

Technical Information

Operating Temperature Min	-4 °F	Compatibility	LMJA-8XXX, LMJA-9XXX
Number of Connections	2	Operating Temperature Max	140 °F
Indicator	Power LED, Receive LED, Transmit LED	Connector Type	RS-485
Indoor/Outdoor	Indoor	Mounting Type	DIN Rail
Operating Temperature	-20°-60°C, -4°-140°F	Operating Humidity	5-95% RH (Non-Condensing)
Storage Temperature	-40° - 85° C		