



## Wattstopper Closed Loop Single Zone DLM photosensor w/extended tube Part No. LMLS-400-L



The LMLS-400 is a closed loop photosensor that measures the ambient light level in order to automatically switch or dim one zone of lighting. It is part of a Digital Lighting Management (DLM) system and sends light level signals to control loads connected to DLM on/off or dimming room controllers. The LMLS-400 has a photodiode with an extended range of 1-1,553.

## Features & Benefits

Daylight responsive on/off, bi-level, tri-level or dimming control for one lighting zone

Extended tube model accommodates thicker ceiling materials

100 degree spatial response for optimal detection of ambient light level

Automatic calibration and configuration; optional hold off setting to maximize energy savings

Photodiode corrected to match the photopic response of the human eye

Can be calibrated in any daylight condition

## Specifications

### General Info

Product Line	Wattstopper	Color	White
Finish	Glossy	UPC Number	754182932153
Country Of Origin	China	Product Series	LMLS
Features	Fits Ceiling Tiles from 5/8-1.25 in, Single Zone	Installation Location	Ceiling
Application Sector	Commercial	Standard	RoHS, UL, FCC part 15
Warranty Type	5-Year	Type	Sensor

### Dimensions

Product Width US	1.1 in	Product Weight US	0.1 lb
------------------	--------	-------------------	--------

Product Volume US	36.1 cu in	Product Depth US	1.5 in
Product Height US	4.0 in		

Additional Information

RoHS Compliant	Yes		
----------------	-----	--	--

Technical Information

Operating Temperature Min	32 F	Compatibility	DLM Wired, Infrared Wireless
Has Battery	No	Control Algorithm	Closed Loop
Sensor Coverage Pattern	100 deg	Sensor Type	Daylight
Operating Temperature Max	131 F	Sensor Technology	Photosensor
Topology	Free Topology	Connector Type	RJ-45
Input Voltage	24 VDC	Indoor/Outdoor	Indoor
Mounting Type	0.9 in Knockout	Current Draw	7 mA
Operating Temperature	32°-131°F	Operating Humidity	5-95% RH (Non- Condensing)
Sensing Range	1-1553 fc	Storage Temperature	23° - 140° F