



The LMIO-301 photocell input module is an accessory for a networked Digital Lighting Management (DLM) installation that allows an LMSM segment manager or LMCP panel to read ambient light levels for use in controlling exterior lighting or interior lighting installed in brightly daylit spaces such as atriums. The LMIO-301 works in conjunction with either the LMPO-200 exterior or LMPS-6000 skylight low voltage photocell heads.

Features & Benefits

Module and selected photocell read light levels for exterior or interior applications	Works with LMSM segment manager or LMCP panel
Connects to segment network via DLM local network connection	Compatible with LMCP panels and LMSM segment managers
DIN rail clamp allows mounting in LMCP Series panel	Works with a choice of photocells for exterior and skylight locations

Specifications

General Info

Product Line	Wattstopper	Color	White
Finish	Glossy	UPC Number	754182931071
Country Of Origin	United States	Product Series	LMPO
Features	Single Zone	Installation Location	Outdoor J-Box
Application Sector	Commercial	Standard	UL, FCC part 15, RoHS
Warranty Type	5-Year	Type	Photocell

Dimensions

Product Width US	1.3 in	Product Weight US	1.0 oz
Product Volume US	4.7 cu in	Product Depth US	1.3 in

Product Height US	2.8 in
-------------------	--------

Technical Information

Operating Temperature Min	-40 F	Compatibility	LMIN-104
---------------------------	-------	---------------	----------

Has Battery	No	Control Algorithm	Open Loop
-------------	----	-------------------	-----------

Sensor Type	Daylight	Operating Temperature Max	140 F
-------------	----------	---------------------------	-------

Sensor Technology	Photosensor	Connector Type	Wire Leads
-------------------	-------------	----------------	------------

Input Voltage	24 VDC	Indoor/Outdoor	Outdoor
---------------	--------	----------------	---------

Mounting Type	Watertight J-Box	Current Draw	5 mA
---------------	------------------	--------------	------

Operating Temperature	-40°-140°F	Sensing Range	0-200 fc
-----------------------	------------	---------------	----------

Storage Temperature	23° - 140° F
---------------------	--------------
